




Doing Our Best to Provide You the Best

8A000014, Rev AC
07/24

BIN FILL AUGER (BFA) EXTENDER 2010

9A000051 = BFA EXTENDER 2010 COMPLETE ASSEMBLY



INSTRUCTION MANUAL

DEMCO - BIN FILL AUGER (BFA) EXTENDER 2010

9A000051 = BFA Extender 2010 Complete Assembly

BOM ID	Qty	Item No	Description
1	1	R5A000004L0	Cross Pipe Assembly
2	1	R3A000079L0	16" BFA Extender Pipe
3	1	1AR00000100	Plastic Barrel Plug - 2.130" Dia.



WARNING:
TO AVOID PERSONAL INJURY OR DEATH,
OBSERVE THE FOLLOWING INSTRUCTIONS:

- Beware of and avoid contact with low power lines and other obstructions while operating combines equipped with the Demco Bin Fill Auger and BFA Extender.
- Collapse and secure the Bin Fill Auger when transporting the combine to avoid contact with low power lines and other obstructions.

ASSEMBLY INSTRUCTIONS:

- 1) Loosen (2) set screws that connect the main auger assembly to the existing cross pipe pivot.
- 2) Remove the main auger assembly.
- 3) Rotate existing cross pipe pivot to vertical position. See Figure 19.
- 4) Insert 16" BFA extender pipe in existing cross pipe pivot. Tighten all set screws in existing cross pipe pivot.
- 5) Install plastic barrel plug in the top of the of the 16" extender pipe.
- 6) Slide new cross pipe assembly over 16" extender pipe. Adjust to preferred position and height, and tighten the two sets crews.
- 7) Attach main auger assembly to new cross pipe assembly, and tighten the two remaining set screws.
- 8) Tighten all jam nuts on set screws to secure Bin Fill Auger and BFA Extender assemblies.




Figure 18




Figure 19

NOTE: Set your Bin Fill Auger to the position which best fits your application. Make sure that the auger will not interfere or come in contact with any other braces, brackets, or augers inside the combine tank. Insure there is plenty of clearance for the Bin Fill Auger to rotate between both the folded and the upright positions.

If you have questions not answered in this manual or require a replacement manual, please contact your dealer or call 1-800-54DEMCO (800-543-3626).



4010 320th St., Boyden, IA. 51234

Phone: (712) 725-2311

Fax: (712) 725-2380

Toll Free: 1-800-54DEMCO (1-800-543-3626)

**Demco warranty policies, operator manuals, and product registration
can be found online:**

www.demco-products.com